



Temperature Conversion Chart

In the center column, find the number which corresponds to the base temperature to be converted. The Celsius equivalent temperature to a Fahrenheit base temperature is in the left column. The Fahrenheit equivalent temperature to a Celsius base temperature is in the right column.

Temperature Conversion Chart													
°C	°F	°C	°F	°C	°F	°C	°F	°C	°F	°C	°F	°C	°F
40	-40	-10	14	20	68	50	122	80	176	110	230	140	284
-39	-38.2	-9	15.8	21	69.8	51	123.8	81	177.8	111	231.8	141	285.8
-38	-36.4	-8	17.6	22	71.6	52	125.6	82	179.6	112	233.6	142	287.6
-37	-34.6	-7	19.4	23	73.4	53	127.4	83	181.4	113	235.4	143	289.4
-36	-32.8	-6	21.2	24	75.2	54	129.2	84	183.2	114	237.2	144	291.2
-35	-31	-5	23	25	77	55	131	85	185	115	239	145	293
-34	29.2	-4	24.8	26	78.8	56	132.8	86	186.8	116	240.8	146	294.8
-33	-27.4	-3	26.6	27	80.6	57	134.6	87	188.6	117	242.6	147	296.6
-32	-25.6	-2	28.4	28	82.4	58	136.4	88	190.4	118	244.4	148	298.4
-31	-23.8	-1	30.2	29	84.2	59	138.2	89	192.2	119	246.2	149	300.2
-30	-22	0	32	30	86	60	140	90	194	120	248	150	302
-29	-20.2	1	33.8	31	87.8	61	141.8	91	195.8	121	249.8	151	303.8
-28	-18.4	2	35.6	32	89.6	62	143.6	92	197.6	122	251.6	152	305.6
-27	-16.6	3	37.4	33	91.4	63	145.4	93	199.4	123	253.4	153	307.4
-26	-14.8	4	39.2	34	93.2	64	147.2	94	201.2	124	255.2	154	309.2
-25	-13	5	41	35	95	65	149	95	203	125	257	155	311
-24	-11.2	6	42.8	36	96.8	66	150.8	96	204.8	126	258.8	156	312.8
-23	-9.4	7	44.6	37	98.6	67	152.6	97	206.6	127	260.6	157	314.6
-22	-7.6	8	46.4	38	100.4	68	154.4	98	208.4	128	262.4	158	316.4
-21	-5.8	9	48.2	39	102.2	69	156.2	99	210.2	129	264.2	159	318.2
-20	-4	10	50	40	104	70	158	100	212	130	266	160	320
-19	-2.2	11	51.8	41	105.8	71	159.8	101	213.8	131	267.8	161	321.8
-18	-0.4	12	53.6	42	107.6	72	161.6	102	215.6	132	269.6	162	323.6
-17	1.4	13	55.4	43	109.4	73	163.4	103	217.4	133	271.4	163	325.4
-16	3.2	14	57.2	44	111.2	74	165.2	104	219.2	134	273.2	164	327.2
-15	5	15	59	45	113	75	167	105	221	135	275	165	329
-14	6.8	16	60.8	46	114.8	76	168.8	106	222.8	136	276.8	166	330.8
-13	8.6	17	62.6	47	116.6	77	170.6	107	224.6	137	278.6	167	332.6
-12	10.4	18	64.4	48	118.4	78	172.4	108	226.4	138	280.4	168	334.4
-11	12.2	19	66.2	49	120.2	79	174.2	109	228.2	139	282.2	169	336.2