



- Notes
- 1) All dimensions are in feet and inches. Weights are in pounds and do not include options and accessories.
 - 2) Unless otherwise indicated, connections 3" and smaller are NPT. Connections 4" and larger are grooved to suit a mechanical coupling and beveled for welding.
 - 3) Dimensions showing location of coil connections are approximate and should not be used for prefabrication of connecting piping.
 - 4) For weight loadings and support requirements, refer to the suggested steel support drawing.
 - 5) The area above the discharge must be unobstructed.
 - 6) Piping must not be supported by the unit inlet or outlet connections.
 - 7) M = Motor location, M1 = Large Motor Location, M2 = Small Motor Location



MODEL NO.	APPROX. SHIPPING WEIGHT	APPROX. OPERATING WEIGHT	HEAVIEST SECTION (COIL)	F	H
VCA-605A	27750	43190	9950	2'-9 1/4"	13'-9 1/2"
VCA-684A	27770	43210	9950	2'-9 1/4"	13'-9 1/2"
VCA-754A	27810	43250	9950	2'-9 1/4"	13'-9 1/2"
VCA-808A	27820	43260	9950	2'-9 1/4"	13'-9 1/2"
VCA-762A	31790	47440	11960	3'-6 1/2"	14'-6 3/4"
VCA-840A	31830	47480	11960	3'-6 1/2"	14'-6 3/4"
VCA-902A	37840	47490	11960	3'-6 1/2"	14'-6 3/4"
VCA-879A	35850	51720	13970	4'-3 3/4"	15'-4"
VCA-942A	35860	51730	13970	4'-3 3/4"	15'-4"
VCA-1026A	35940	51810	13970	4'-3 3/4"	15'-4"
VCA-982A	38340	54350	15210	4'-3 3/4"	15'-4"
VCA-1082A	38420	54430	15210	4'-3 3/4"	15'-4"
VCA-1160A	38730	54740	15210	4'-3 3/4"	15'-4"
VCA-1075A	42590	58840	17340	5'-1"	16'-1 1/4"
VCA-1170A	42670	58920	17340	5'-1"	16'-1 1/4"
VCA-1252A	42840	59090	17340	5'-1"	16'-1 1/4"
VCA-1321A	42980	59230	17340	5'-1"	16'-1 1/4"

ORDER NO: _____

DATE: _____



Baltimore Aircoil

VCA Unit Print
12'x24' RH
DRAWING NUMBER: _____