



Nexus® Engineering Data



NXF-0403N Models



NXF-0603N Models


**NOTES:**

1. Nominal tons of cooling represents 3 USGPM of water cooled from 95°F to 85°F at a 78°F entering wet-bulb temperature.
2. For structural support, contact your local BAC representative.

Do not use for construction.

Refer to factory certified dimensions.

This catalog includes data current at the time of publication, which should be reconfirmed at the time of purchase. Up-to-date engineering data, free product selection software, and more can be found at BaltimoreAircoil.com.



NXF-0x03N-xxxx-x6 Shown

Model Number	Number of Modules	Nominal Tons ⁽¹⁾	Fan Motor HP	Pump Motor HP	Airflow (CFM)	Spray Pump USGPM	Operating Weight (lbs)	Shipping Weight (lbs)	hCore Internal Volume (Gal)	L	W	H
NXF-0403N-CS2TT-H1	1	20	(1) 5	(1) 1/2	8,416	32	2,661	2,272	26	3'-3 1/2"	4'-1 1/2"	8'-6"
NXF-0403N-CS2TT-H2	2	40	(2) 5	(2) 1/2	16,832	64	5,275	4,416	52	6'-7"		
NXF-0403N-CS2TT-H3	3	60	(3) 5	(3) 1/2	25,248	96	7,800	6,512	78	9'-10 1/2"		
NXF-0403N-CS2TT-H4	4	80	(4) 5	(4) 1/2	33,664	128	10,417	8,653	105	13'-2"		
NXF-0403N-CS2TT-H5	5	100	(5) 5	(5) 1/2	42,080	160	13,025	10,785	131	16'-5 1/2"		
NXF-0403N-CS2TT-H6	6	120	(6) 5	(6) 1/2	50,496	192	15,633	12,916	157	19'-9"		
NXF-0603N-CS2TT-J1	1	30	(2) 3.75	(1) 1/2	12,888	50	3,763	3,190	39	3'-3 1/2"	5'-11 1/2"	8'-6"
NXF-0603N-CS2TT-J2	2	60	(4) 3.75	(2) 1/2	25,776	100	7,480	6,253	78	6'-7"		
NXF-0603N-CS2TT-J3	3	90	(6) 3.75	(3) 1/2	38,664	150	11,106	9,266	117	9'-10 1/2"		
NXF-0603N-CS2TT-J4	4	120	(8) 3.75	(4) 1/2	51,552	200	14,826	12,326	156	13'-2"		
NXF-0603N-CS2TT-J5	5	150	(10) 3.75	(5) 1/2	64,440	250	18,536	15,376	195	16'-5 1/2"		
NXF-0603N-CS2TT-J6	6	180	(12) 3.75	(6) 1/2	77,328	300	22,246	18,426	234	19'-9"		