



# BAC Nexus™ Modular Hybrid Cooler Pressure Drop for Coils

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
NXF-0403N-CS2TS-H1	Water	90	1.2	2.5" x 2	72	0.8	2.5" x 2	108	1.7	2.5"x2
NXF-0403N-CS2TS-H1	30% Ethylene Glycol	90	1.5	2.5" x 2	72	1.0	2.5" x 2	108	2.0	2.5"x2
NXF-0403N-CS2TS-H1	30% Propylene Glycol	90	1.5	2.5" x 2	72	1.0	2.5" x 2	108	2.1	2.5"x2
NXF-0403N-CS2TT-H1	Water	90	6.2	2.5" x 1	72	4.1	2.5" x 1	108	8.5	2.5"x1
NXF-0403N-CS2TT-H1	30% Ethylene Glycol	90	7.3	2.5" x 1	72	4.9	2.5" x 1	108	10.1	2.5"x1
NXF-0403N-CS2TT-H1	30% Propylene Glycol	90	7.4	2.5" x 1	72	5.0	2.5" x 1	108	10.3	2.5"x1
NXF-0603N-CS2TS-J1	Water	130	0.6	2.5" x 2	104	0.4	2.5" x 2	156	0.8	2.5"x2
NXF-0603N-CS2TS-J1	30% Ethylene Glycol	130	0.7	2.5" x 2	104	0.5	2.5" x 2	156	1.0	2.5"x2
NXF-0603N-CS2TS-J1	30% Propylene Glycol	130	0.7	2.5" x 2	104	0.5	2.5" x 2	156	1.0	2.5"x2
NXF-0603N-CS2TT-J1	Water	130	8.3	2.5" x 1	104	5.5	2.5" x 1	156	11.5	2.5"x1
NXF-0603N-CS2TT-J1	30% Ethylene Glycol	130	9.8	2.5" x 1	104	6.6	2.5" x 1	156	13.7	2.5"x1
NXF-0603N-CS2TT-J1	30% Propylene Glycol	130	10.0	2.5" x 1	104	6.7	2.5" x 1	156	13.9	2.5"x1
NXF-0403E-CS2TS-H1	Water	90	1.2	2.5" x 2	72	0.8	2.5" x 2	108	1.7	2.5"x2
NXF-0403E-CS2TS-H1	30% Ethylene Glycol	90	1.5	2.5" x 2	72	1.0	2.5" x 2	108	2.0	2.5"x2
NXF-0403E-CS2TS-H1	30% Propylene Glycol	90	1.5	2.5" x 2	72	1.0	2.5" x 2	108	2.1	2.5"x2
NXF-0403E-CS2TT-H1	Water	90	6.2	2.5" x 1	72	4.1	2.5" x 1	108	8.5	2.5"x1
NXF-0403E-CS2TT-H1	30% Ethylene Glycol	90	7.3	2.5" x 1	72	4.9	2.5" x 1	108	10.1	2.5"x1
NXF-0403E-CS2TT-H1	30% Propylene Glycol	90	7.4	2.5" x 1	72	5.0	2.5" x 1	108	10.3	2.5"x1
NXF-0603E-CS2TS-J1	Water	130	0.6	2.5" x 2	104	0.4	2.5" x 2	156	0.8	2.5"x2
NXF-0603E-CS2TS-J1	30% Ethylene Glycol	130	0.7	2.5" x 2	104	0.5	2.5" x 2	156	1.0	2.5"x2
NXF-0603E-CS2TS-J1	30% Propylene Glycol	130	0.7	2.5" x 2	104	0.5	2.5" x 2	156	1.0	2.5"x2
NXF-0603E-CS2TT-J1	Water	130	8.3	2.5" x 1	104	5.5	2.5" x 1	156	11.5	2.5"x1
NXF-0603E-CS2TT-J1	30% Ethylene Glycol	130	9.8	2.5" x 1	104	6.6	2.5" x 1	156	13.7	2.5"x1
NXF-0603E-CS2TT-J1	30% Propylene Glycol	130	10.0	2.5" x 1	104	6.7	2.5" x 1	156	13.9	2.5"x1