



FXV Closed Circuit Cooling Tower Performance at Standard Conditions

Table with columns for Condition Reference #, Wet Bulb °F, Range °F, Approach °F, Inlet Water Temperature °F, Outlet Water Temperature °F, and 48 GPM flow rates.

Main performance data table with columns for Model (e.g., FXV-0806A-12D-G), Inlet Water Temperature °F, Outlet Water Temperature °F, and 48 GPM flow rates.



FXV Closed Circuit Cooling Tower Performance at Standard Conditions

Table with columns for Condition Reference #, Wet Bulb °F, Range °F, Approach °F, Inlet Water Temperature °F, Outlet Water Temperature °F, and 48 numbered columns representing different performance metrics.



FXV Closed Circuit Cooling Tower Performance at Standard Conditions

Table with columns for Condition Reference #, Wet Bulb °F, Range °F, Approach °F, Inlet Water Temperature °F, Outlet Water Temperature °F, and 48 numbered columns for performance data points.



FVX Closed Circuit Cooling Tower Performance at Standard Conditions

Table with columns for Condition Reference #, Wet Bulb °F, Range °F, Approach °F, Inlet Water Temperature °F, Outlet Water Temperature °F, and 48 numbered columns representing different operating points. The table contains a dense grid of numerical data points.





FXV Closed Circuit Cooling Tower Performance at Standard Conditions

Table with 47 columns (Condition Reference #, 1-47) and 47 rows (Wet Bulb °F, Range °F, Approach °F, Inlet Water Temperature °F, Outlet Water Temperature °F, FXV-0806B-28D-J, FXV-0806B-28D-K, FXV-0806B-28D-L, FXV-0806B-32D-G, FXV-0806B-32D-H, FXV-0806B-32D-I, FXV-0806B-32D-J, FXV-0806B-32D-K, FXV-0806B-32D-L, FXV-0806B-32D-M, FXV-0806B-36D-G, FXV-0806B-36D-H, FXV-0806B-36D-I, FXV-0806B-36D-J, FXV-0806B-36D-K, FXV-0806B-36D-L, FXV-0806B-36D-M, FXV-0809A-12D-G, FXV-0809A-12D-H, FXV-0809A-12D-I, FXV-0809A-12D-J, FXV-0809A-16D-G, FXV-0809A-16D-H, FXV-0809A-16D-I, FXV-0809A-16D-J, FXV-0809A-20D-G, FXV-0809A-20D-H, FXV-0809A-20D-I, FXV-0809A-20D-J, FXV-0809A-24D-G, FXV-0809A-24D-H, FXV-0809A-24D-I, FXV-0809A-24D-J, FXV-0809B-16D-G, FXV-0809B-16D-H, FXV-0809B-16D-I, FXV-0809B-16D-J, FXV-0809B-20D-G, FXV-0809B-20D-H, FXV-0809B-20D-I, FXV-0809B-20D-J, FXV-0809B-24D-G, FXV-0809B-24D-H, FXV-0809B-24D-I, FXV-0809B-24D-J, FXV-0809B-28D-G, FXV-0809B-28D-H, FXV-0809B-28D-I, FXV-0809B-28D-J, FXV-0809B-32D-G, FXV-0809B-32D-H, FXV-0809B-32D-I, FXV-0809B-32D-J, FXV-0809B-36D-G, FXV-0809B-36D-H, FXV-0809B-36D-I, FXV-0809B-36D-J, FXV-0809B-40D-G, FXV-0809B-40D-H, FXV-0809B-40D-I, FXV-0809B-40D-J, FXV-0812A-12D-K, FXV-0812A-12D-L, FXV-0812A-12D-M, FXV-0812A-16D-J, FXV-0812A-16D-K, FXV-0812A-16D-L, FXV-0812A-16D-M, FXV-0812A-16D-N, FXV-0812A-20D-J, FXV-0812A-20D-K, FXV-0812A-20D-L, FXV-0812A-20D-M, FXV-0812A-20D-N, FXV-0812A-23G-K



FXV Closed Circuit Cooling Tower Performance at Standard Conditions

Table with columns for Condition Reference #, Wet Bulb °F, Range °F, Approach °F, Inlet Water Temperature °F, Outlet Water Temperature °F, and 48 numbered columns representing different operating conditions. The table contains performance data for various cooling tower models and configurations.







FXV Closed Circuit Cooling Tower Performance at Standard Conditions

Table with columns for Wet Bulb °F, Range °F, Approach °F, Inlet Water Temperature °F, Outlet Water Temperature °F, and 48 numbered columns (1-48) representing various performance metrics.



FXV Closed Circuit Cooling Tower Performance at Standard Conditions

Table with columns for Condition Reference #, Wet Bulb °F, Range °F, Approach °F, Inlet Water Temperature °F, Outlet Water Temperature °F, and 49 numbered columns (1-49) representing various performance metrics. The table is divided into sections for 30% Propylene Glycol and 30% Ethylene Glycol.



FXV Closed Circuit Cooling Tower Performance at Standard Conditions

Table with 48 columns (Condition Reference #, Wet Bulb °F, Range °F, Approach °F, Inlet Water Temperature °F, Outlet Water Temperature °F) and 48 rows of data for various cooling tower models (FXV-0809B-20D-H to FXV-0812B-24Q-J).



FXV Closed Circuit Cooling Tower Performance at Standard Conditions

Table with 48 columns (Condition Reference #, 1-48) and 48 rows (Wet Bulb °F, Range °F, Approach °F, Inlet Water Temperature °F, Outlet Water Temperature °F, FXV-0812B-24Q-K, FXV-0812B-24Q-L, FXV-0812B-24Q-M, FXV-0812B-24Q-N, FXV-0812B-24Q-O, FXV-0812B-24T-K, FXV-0812B-24T-L, FXV-0812B-24T-M, FXV-0812B-24T-N, FXV-0812B-24T-O, FXV-0812B-28D-K, FXV-0812B-28D-L, FXV-0812B-28D-M, FXV-0812B-28D-N, FXV-0812B-28D-O, FXV-0812B-30T-K, FXV-0812B-30T-L, FXV-0812B-30T-M, FXV-0812B-30T-N, FXV-0812B-30T-O, FXV-0812B-32Q-K, FXV-0812B-32Q-L, FXV-0812B-32Q-M, FXV-0812B-32Q-N, FXV-0812B-32Q-O, FXV-0812B-36T-J, FXV-0812B-36T-K, FXV-0812B-36T-L, FXV-0812B-36T-M, FXV-0812B-36T-N, FXV-0812B-36T-O, FXV-081A-12D-K, FXV-081A-12D-L, FXV-081A-12D-M, FXV-081A-12D-N, FXV-081A-12D-O, FXV-081A-16Q-K, FXV-081A-16Q-L, FXV-081A-16Q-M, FXV-081A-16Q-N, FXV-081A-16Q-O, FXV-081A-20Q-K, FXV-081A-20Q-L, FXV-081A-20Q-M, FXV-081A-20Q-N, FXV-081A-20Q-O, FXV-081A-24Q-K, FXV-081A-24Q-L, FXV-081A-24Q-M, FXV-081A-24Q-N, FXV-081A-24Q-O, FXV-081A-28Q-K, FXV-081A-28Q-L, FXV-081A-28Q-M, FXV-081A-28Q-N, FXV-081A-28Q-O, FXV-081A-32Q-K, FXV-081A-32Q-L, FXV-081A-32Q-M, FXV-081A-32Q-N, FXV-081A-32Q-O, FXV-081A-36Q-K, FXV-081A-36Q-L, FXV-081A-36Q-M, FXV-081A-36Q-N, FXV-081A-36Q-O, FXV-081B-12D-K, FXV-081B-12D-L, FXV-081B-12D-M, FXV-081B-12D-N, FXV-081B-12D-O, FXV-081B-16Q-K, FXV-081B-16Q-L, FXV-081B-16Q-M, FXV-081B-16Q-N, FXV-081B-16Q-O, FXV-081B-20Q-K, FXV-081B-20Q-L, FXV-081B-20Q-M, FXV-081B-20Q-N, FXV-081B-20Q-O, FXV-081B-24Q-K, FXV-081B-24Q-L, FXV-081B-24Q-M, FXV-081B-24Q-N, FXV-081B-24Q-O, FXV-081B-28Q-K, FXV-081B-28Q-L, FXV-081B-28Q-M, FXV-081B-28Q-N, FXV-081B-28Q-O, FXV-081B-32Q-K, FXV-081B-32Q-L, FXV-081B-32Q-M, FXV-081B-32Q-N, FXV-081B-32Q-O, FXV-081B-36Q-K, FXV-081B-36Q-L, FXV-081B-36Q-M, FXV-081B-36Q-N, FXV-081B-36Q-O, FXV-1212B-12D-K, FXV-1212B-12D-L, FXV-1212B-12D-M, FXV-1212B-12D-N, FXV-1212B-12D-O, FXV-1212B-16Q-K, FXV-1212B-16Q-L, FXV-1212B-16Q-M, FXV-1212B-16Q-N, FXV-1212B-16Q-O, FXV-1212B-20Q-K, FXV-1212B-20Q-L, FXV-1212B-20Q-M, FXV-1212B-20Q-N, FXV-1212B-20Q-O, FXV-1212B-24Q-K, FXV-1212B-24Q-L, FXV-1212B-24Q-M, FXV-1212B-24Q-N, FXV-1212B-24Q-O, FXV-1212B-28Q-K, FXV-1212B-28Q-L, FXV-1212B-28Q-M, FXV-1212B-28Q-N, FXV-1212B-28Q-O, FXV-1212B-32Q-K, FXV-1212B-32Q-L, FXV-1212B-32Q-M, FXV-1212B-32Q-N, FXV-1212B-32Q-O, FXV-1212B-36Q-K, FXV-1212B-36Q-L, FXV-1212B-36Q-M, FXV-1212B-36Q-N, FXV-1212B-36Q-O, FXV-1212B-40Q-K, FXV-1212B-40Q-L, FXV-1212B-40Q-M, FXV-1212B-40Q-N, FXV-1212B-40Q-O, FXV-1212B-44Q-K, FXV-1212B-44Q-L, FXV-1212B-44Q-M, FXV-1212B-44Q-N, FXV-1212B-44Q-O, FXV-1212B-48Q-K, FXV-1212B-48Q-L, FXV-1212B-48Q-M, FXV-1212B-48Q-N, FXV-1212B-48Q-O





FXV Closed Circuit Cooling Tower Performance at Standard Conditions

Table with columns for Condition Reference #, Wet Bulb °F, Range °F, Approach °F, Inlet Water Temperature °F, Outlet Water Temperature °F, and 49 numbered columns representing different performance metrics.