



- Notes
- 1) Drawings are not to scale. All dimensions are in feet and inches.
 - 2) Unless otherwise indicated, connections 3" and smaller are MPT. Connections 4" and larger are grooved to suit a mechanical coupling and beveled for welding.
 - 3) Dimensions showing location of coil and basin connections are approximate and should not be used for prefabrication of connecting piping.
 - 4) For weight loadings and support requirements, refer to the suggested steel support drawing.
 - 5) Heaviest section is the combined weight of fan and coil sections, refer to the P-Series Counterflow Induced Draft Coil Products rigging and assembly manual for suggested lifting method.
 - 6) The area above the discharge must be unobstructed.
 - 7) Do not support piping from unit connections. All necessary piping supports to be supplied by others.
 - 8) M = Motor location

| Model Number | Approx. Shipping Weight | Approx. Operating Weight | Heaviest Section Weight | F | H |
|-------------------|-------------------------|--------------------------|-------------------------|------------|------------|
| PCC-0538-1024N060 | 25320 | 37230 | 10430 | 4'-0 5/8" | 16'-5 5/8" |
| PCC-0416-1024N020 | 25590 | 37550 | 10560 | 4'-0 5/8" | 16'-5 5/8" |
| PCC-0466-1024N030 | 25840 | 37800 | 10690 | 4'-0 5/8" | 16'-5 5/8" |
| PCC-0544-1024N040 | 29670 | 41790 | 12600 | 5'-11 1/8" | 18'-4 1/8" |
| PCC-0562-1024N050 | 28740 | 40860 | 12140 | 4'-8 1/8" | 17'-1 1/8" |
| PCC-0590-1024N060 | 28840 | 40960 | 12190 | 4'-8 1/8" | 17'-1 1/8" |
| PCC-0630-1024N080 | 30260 | 42440 | 12900 | 4'-8 1/8" | 17'-1 1/8" |
| PCC-0646-1024N060 | 35890 | 48400 | 15710 | 5'-11 1/8" | 18'-4 1/8" |
| PCC-0492-1024N020 | 36920 | 49530 | 16220 | 5'-11 1/8" | 18'-4 1/8" |
| PCC-0656-1024N060 | 37490 | 50110 | 16510 | 5'-11 1/8" | 18'-4 1/8" |

FACE C

ORDER NO:

DATE:



BALTIMORE AIRCOIL COMPANY

**PCC Evaporative Condenser
Tabulated Unit Print**

DRAWING NUMBER:
UP-PCC-1024