


Notes

- 1) All dimensions are in feet and inches. Weights are in pounds and do not include options and accessories.
- 2) Unless otherwise indicated, connections 3" and smaller are NPT. Connections 4" and larger are grooved to suit a mechanical coupling and beveled for welding.
- 3) Dimensions showing location of coil connections are approximate and should not be used for prefabrication of connecting piping.
- 4) For weight loadings and support requirements, refer to the suggested steel support drawing.
- 5) The area above the discharge must be unobstructed.
- 6) Piping must not be supported by the unit inlet or outlet connections.
- 7) M = Motor location, M1 = Large Motor Location, M2 = Small Motor Location

MODEL NO.	APPROX. SHIPPING WEIGHT	APPROX. OPERATING WEIGHT	HEAVIEST SECTION (COIL)	F	H
VCA-930A	40190	63590	14480	2'-9 1/4"	13'-9 1/2"
VCA-1052A	40210	63610	14480	2'-9 1/4"	13'-9 1/2"
VCA-1162A	40250	63650	14480	2'-9 1/4"	13'-9 1/2"
VCA-1246A	40270	63670	14480	2'-9 1/4"	13'-9 1/2"
VCA-1284A	46220	69940	17460	3'-6 1/2"	14'-6 3/4"
VCA-1376A	46240	69960	17460	3'-6 1/2"	14'-6 3/4"
VCA-1204A	52150	76190	20450	4'-3 3/4"	15'-4"
VCA-1327A	52190	76230	20450	4'-3 3/4"	15'-4"
VCA-1422A	52210	76250	20450	4'-3 3/4"	15'-4"
VCA-1570A	52290	76330	20450	4'-3 3/4"	15'-4"
VCA-1501A	56000	80270	22340	4'-3 3/4"	15'-4"
VCA-1654A	56080	80350	22340	4'-3 3/4"	15'-4"
VCA-1774A	56330	80600	22340	4'-3 3/4"	15'-4"
VCA-1790A	62490	87120	25550	5'-1"	16'-1 1/4"
VCA-1914A	62740	87370	25550	5'-1"	16'-1 1/4"
VCA-2019A	62870	87500	25550	5'-1"	16'-1 1/4"



ORDER NO: _____

DATE: _____



Baltimore Aircoil

VCA Unit Print
12'x36' RH
DRAWING NUMBER: _____