



PLAN VIEW

PLAN "C" STEEL

Model Number	Shipping Weight	Operating Weight
PT2-1009A-1x2	8780	15670
PT2-1009A-2x2	9520	16410
PT2-1009A-3x2	10200	17090
PT2-1009A-4x2	10680	18640
PT2-1009A-5x2	11240	19210

Notes

- 1) All dimensions are in feet and inches. Weights are in pounds and include options and accessories.
- 2) Supporting steelwork and anchor bolts to be designed and furnished by others.
- 3) All supporting steel must be flush and level at top.
- 4) Each beam should be designed, as a minimum, for 65% of the total unit operating weight applied as a uniformly distributed load.
- 5) Beams should be selected in accordance with accepted structural practice, maximum deflection of beam under unit to be 1/360 of span, not to exceed 1/2 inch.
- 6) If vibration isolation rails are to used between unit and supporting steel, be certain to allow for the length of the vibration rails when determining length of supporting steel. Vibration rail length and mounting hole locations may differ from those of the unit. Refer to vibration isolator drawings for this data.
- 7) Do not use this drawing to size point vibration isolators. See your BAC Representative for details.

ORDER NO:

DATE:



BALTIMORE AIRCOIL COMPANY

**PT2 Two Cell Unit Support
Internal Belt Drive**

DRAWING NUMBER:
GEN-PT2-1009A-SS 2-CELL