




Vertex™ Evaporative Condenser Engineering Data




Face A: Vertex 10' x 12' and 10' x 18'
EC Fan System Units




Face D: Vertex 10' x 12'
EC Fan System Units




Face D: Vertex 10' x 18'
EC Fan System Units



Face A: Vertex 10' x 12' and 10' x 18' Units
Baltidrive® Power Train Units



Face D: Vertex 10' x 12'
Baltidrive® Power Train Units



Face D: Vertex 10' x 18' Units
Baltidrive® Power Train Units

NOTES:


1. Model number denotes nominal tons using R-717 tons are at a 96.3°F condensing temperature, a 20°F suction temperature, and a 78°F entering wet-bulb temperature.
2. R-22 tons are at a 105°F condensing temperature, a 40°F suction temperature, and a 78°F entering wet-bulb temperature.
3. Unless otherwise noted, the coil section is the heaviest section.
4. Operating weight is for the unit with the water level at the overflow level and with the coil charged with R-717.
5. The R-22 operating charge is 1.93 times the R-717 charge; R-134a is 1.98 times.
6. Drain size is based on a bottom connection.
7. Coil inlet and outlet connections are 4" beveled for welding.

Do not use for construction. Refer to factory certified dimensions. This catalog includes data current at the time of publication, which should be reconfirmed at the time of purchase.




Nom. Box Size	Model Number ^[1]	Base Heat Rejection (MBH)	R-22 Tons ^[2]	Fan Motor (HP)	Airflow Rate (CFM)	Pump Motor (HP)	Spray Flow Rate (GPM)	Approximate Weight (lbs)			R-717 Operating Charge ^[5] (lbs)	Internal Coil Volume (ft³)	Remote Sump			F	H
								Ship Weight	Heaviest Section ^[3]	Oper. Weight ^[4]			Drain Size ^[6] (in)	Volume Req. (gal)	Approx. Oper. Weight (lbs)		
10' x 12' - EC Fan System	VRC-0241A-1012N-GB	4,986	339	(6) 2.6	70,700	5	500	11,990	7,350	16,330	345	42	8	313	14,530	2'-4 1/4"	14'-5"
	VRC-0269A-1012N-HB	5,569	379	(6) 4.3	83,400			12,050	7,350	16,390	345	42			14,600	2'-4 1/4"	14'-5"
	VRC-0297A-1012N-JB	6,156	419	(6) 6.7	96,800			12,150	7,350	16,490	345	42			14,700	2'-4 1/4"	14'-5"
	VRC-0270A-1012N-GB	5,572	379	(6) 2.6	64,100			13,340	8,700	17,760	427	52			15,960	2'-11 3/4"	15'-0"
	VRC-0301A-1012N-HB	6,223	423	(6) 4.3	75,500			13,400	8,700	17,820	427	52			16,030	2'-11 3/4"	15'-0"
	VRC-0332A-1012N-JB	6,880	468	(6) 6.7	87,600			13,500	8,700	17,920	427	52			16,130	2'-11 3/4"	15'-0"
	VRC-0289A-1012N-GB	5,974	406	(6) 2.6	53,100			15,610	10,970	20,170	566	69			18,360	3'-7"	15'-8"
	VRC-0323A-1012N-HB	6,671	454	(6) 4.3	62,600			15,670	10,970	20,230	566	69			18,430	3'-7"	15'-8"
	VRC-0356A-1012N-JB	7,375	502	(6) 6.7	72,600			15,770	10,970	20,330	566	69			18,530	3'-7"	15'-8"
	VRC-0310A-1012N-GB	6,419	437	(6) 2.6	54,800			17,110	12,470	21,760	658	80			19,960	4'-2 1/2"	16'-3"
	VRC-0346A-1012N-HB	7,169	488	(6) 4.3	64,600			17,170	12,470	21,820	658	80			20,030	4'-2 1/2"	16'-3"
	VRC-0383A-1012N-JB	7,925	539	(6) 6.7	74,900			17,270	12,470	21,920	658	80			20,130	4'-2 1/2"	16'-3"
10' x 12' - BALTDRIVE®	VRC-0213A-1012N-HA	4,410	300	(2) 5	59,800	5	500	12,840	7,350	17,160	345	42	8	313	15,390	2'-4 1/4"	14'-5"
	VRC-0235A-1012N-JA	4,866	331	(2) 7.5	68,500			12,910	7,350	17,230	345	42			15,450	2'-4 1/4"	14'-5"
	VRC-0242A-1012N-HA	4,998	340	(2) 5	55,400			14,190	8,700	18,590	427	52			16,820	2'-11 3/4"	15'-0"
	VRC-0266A-1012N-JA	5,513	375	(2) 7.5	63,400			14,260	8,700	18,660	427	52			16,880	2'-11 3/4"	15'-0"
	VRC-0285A-1012N-KA	5,909	402	(2) 10	69,800			14,280	8,700	18,680	427	52			16,900	2'-11 3/4"	15'-0"
	VRC-0286A-1012N-JA	5,895	401	(2) 7.5	54,500			16,530	10,970	21,070	566	69			19,280	3'-7"	15'-8"
	VRC-0305A-1012N-KA	6,306	429	(2) 10	60,000			16,550	10,970	21,090	566	69			19,300	3'-7"	15'-8"
	VRC-0336A-1012N-LA	6,953	473	(2) 15	68,600			16,730	10,970	21,270	566	69			19,480	3'-7"	15'-8"
	VRC-0279A-1012N-HA	5,777	393	(2) 5	49,900			17,960	12,470	22,590	658	80			20,820	4'-2 1/2"	16'-3"
	VRC-0307A-1012N-JA	6,365	433	(2) 7.5	57,100			18,030	12,470	22,660	658	80			20,880	4'-2 1/2"	16'-3"
	VRC-0330A-1012N-KA	6,821	464	(2) 10	62,800			18,050	12,470	22,680	658	80			20,900	4'-2 1/2"	16'-3"
	VRC-0364A-1012N-LA	7,526	512	(2) 15	71,900			18,230	12,470	22,860	658	80			21,080	4'-2 1/2"	16'-3"
10' x 18' - EC Fan System	VRC-0357A-1018N-GB	7,384	502	(8) 2.6	97,200	7.5	760	16,430	10,440	22,790	513	63	10	456	20,270	2'-4 1/4"	14'-5"
	VRC-0399A-1018N-HB	8,255	562	(8) 4.3	114,600			16,520	10,440	22,880	513	63			20,360	2'-4 1/4"	14'-5"
	VRC-0441A-1018N-JB	9,127	621	(8) 6.7	133,000			16,650	10,440	23,010	513	63			20,490	2'-4 1/4"	14'-5"
	VRC-0389A-1018N-GB	8,060	548	(8) 2.6	90,300			18,410	12,420	24,890	637	78			22,370	2'-11 3/4"	15'-0"
	VRC-0435A-1018N-HB	9,010	613	(8) 4.3	106,500			18,500	12,420	24,980	637	78			22,460	2'-11 3/4"	15'-0"
	VRC-0481A-1018N-JB	9,962	678	(8) 6.7	123,600			18,630	12,420	25,110	637	78			22,590	2'-11 3/4"	15'-0"
	VRC-0426A-1018N-GB	8,812	599	(8) 2.6	74,200			21,720	15,730	28,410	848	104			25,890	3'-7"	15'-8"
	VRC-0476A-1018N-HB	9,849	670	(8) 4.3	87,500			21,810	15,730	28,500	848	104			25,980	3'-7"	15'-8"
	VRC-0526A-1018N-JB	10,889	741	(8) 6.7	101,500			21,940	15,730	28,630	848	104			26,110	3'-7"	15'-8"
	VRC-0457A-1018N-GB	9,470	644	(8) 2.6	76,000			23,910	17,920	30,740	987	121			28,220	4'-2 1/2"	16'-3"
	VRC-0511A-1018N-HB	10,586	720	(8) 4.3	89,600			24,000	17,920	30,830	987	121			28,310	4'-2 1/2"	16'-3"
	VRC-0565A-1018N-JB	11,705	796	(8) 6.7	104,000			24,130	17,920	30,960	987	121			28,440	4'-2 1/2"	16'-3"
10' x 18' - BALTDRIVE®	VRC-0327A-1018N-HA	6,762	460	(3) 5	87,700	7.5	760	17,990	10,440	24,330	513	63	10	456	21,820	2'-4 1/4"	14'-5"
	VRC-0360A-1018N-JA	7,453	507	(3) 7.5	100,400			18,090	10,440	24,430	513	63			21,930	2'-4 1/4"	14'-5"
	VRC-0386A-1018N-KA	7,982	543	(3) 10	110,500			18,130	10,440	24,470	513	63			21,960	2'-4 1/4"	14'-5"
	VRC-0362A-1018N-HA	7,497	510	(3) 5	87,200			19,970	12,420	26,430	637	78			23,920	2'-11 3/4"	15'-0"
	VRC-0399A-1018N-JA	8,232	560	(3) 7.5	95,700			20,070	12,420	26,530	637	78			24,030	2'-11 3/4"	15'-0"
	VRC-0427A-1018N-KA	8,820	600	(3) 10	105,300			20,110	12,420	26,570	637	78			24,060	2'-11 3/4"	15'-0"
	VRC-0347A-1018N-GA	7,174	488	(3) 3	60,300			23,270	15,730	29,940	848	104			27,440	3'-7"	15'-8"
	VRC-0432A-1018N-JA	8,952	609	(3) 7.5	81,800			23,380	15,730	30,050	848	104			27,550	3'-7"	15'-8"
	VRC-0464A-1018N-KA	9,599	653	(3) 10	90,000			23,420	15,730	30,090	848	104			27,580	3'-7"	15'-8"
	VRC-0502A-1018N-KA	10,393	707	(3) 10	94,200			25,610	17,920	32,420	987	121			29,910	4'-2 1/2"	16'-3"
	VRC-0553A-1018N-LA	11,451	779	(3) 15	107,900			25,880	17,920	32,690	987	121			30,170	4'-2 1/2"	16'-3"


Vertex™ Evaporative Condenser Engineering Data




Face A: VRC 12' x 12' and 12' x 18'
EC Fan System Units




Face D: VRC 12' x 12'
EC Fan System Units




Face D: VRC 12' x 18'
EC Fan System Units



Face A: VRC 12' x 12' and 12' x 18'
Baltidrive® Power Train Units



Face D: VRC 12' x 12' Units
Baltidrive® Power Train Units



Face D: VRC 12' x 18'
Baltidrive® Power Train Units

NOTES:


1. Model number denotes nominal tons using R-717 tons are at a 96.3°F condensing temperature, a 20°F suction temperature, and a 78°F entering wet-bulb temperature.
2. R-22 tons are at a 105°F condensing temperature, a 40°F suction temperature, and a 78°F entering wet-bulb temperature.
3. Unless otherwise noted, the coil section is the heaviest section.
4. Operating weight is for the unit with the water level at the overflow level and with the coil charged with R-717.
5. The R-22 operating charge is 1.93 times the R-717 charge; R-134a is 1.98 times.
6. Drain size is based on a bottom connection.
7. Coil inlet and outlet connections are 4" beveled for welding.

Do not use for construction. Refer to factory certified dimensions. This catalog includes data current at the time of publication, which should be reconfirmed at the time of purchase.




Nom. Box Size	Model Number ^[1]	Base Heat Rejection (MBH)	R-22 Tons ^[2]	Fan Motor (HP)	Airflow Rate (CFM)	Pump Motor (HP)	Spray Flow Rate (GPM)	Approximate Weight (lbs)			R-717 Operating Charge ^[5] (lbs)	Internal Coil Volume (ft ³)	Remote Sump			F	H
								Ship Weight	Heaviest Section ^[3]	Oper. Weight ^[4]			Drain Size ^[6] (in)	Volume Req. (gal)	Approx. Oper. Weight (lbs)		
12' x 12' - EC Fan System	VRC-0281A-1212N-GB	5,819	396	(6) 2.6	72,300	5	610	13,840	8,810	18,600	424	52	8	430	17,430	2'-4 1/4"	14'-5"
	VRC-0314A-1212N-HB	6,499	442	(6) 4.3	85,200			13,900	8,810	18,660	424	52			17,490	2'-4 1/4"	14'-5"
	VRC-0348A-1212N-JB	7,184	489	(6) 6.7	98,900			14,000	8,810	18,760	424	52			17,590	2'-4 1/4"	14'-5"
	VRC-0311A-1212N-GB	6,430	437	(6) 2.6	69,600			15,490	10,460	20,350	525	64			19,180	2'-11 3/4"	15'-0"
	VRC-0347A-1212N-HB	7,181	488	(6) 4.3	82,100			15,550	10,460	20,410	525	64			19,240	2'-11 3/4"	15'-0"
	VRC-0383A-1212N-JB	7,938	540	(6) 6.7	95,300			15,650	10,460	20,510	525	64			19,340	2'-11 3/4"	15'-0"
	VRC-0338A-1212N-GB	7,001	476	(6) 2.6	65,500			18,070	13,040	23,090	683	84			21,910	3'-7"	15'-8"
	VRC-0378A-1212N-HB	7,819	532	(6) 4.3	77,200			18,130	13,040	23,150	683	84			21,970	3'-7"	15'-8"
	VRC-0418A-1212N-JB	8,643	588	(6) 6.7	89,700			18,230	13,040	23,250	683	84			22,070	3'-7"	15'-8"
	VRC-0363A-1212N-GB	7,507	511	(6) 2.6	60,900			19,870	14,840	25,010	794	97			23,830	4'-2 1/2"	16'-3"
	VRC-0405A-1212N-HB	8,384	570	(6) 4.3	71,800			19,930	14,840	25,070	794	97			23,890	4'-2 1/2"	16'-3"
	VRC-0448A-1212N-JB	9,268	630	(6) 6.7	83,400			20,030	14,840	25,170	794	97			23,990	4'-2 1/2"	16'-3"
12' x 12' - BALTDRIIVE®	VRC-0214A-1212N-GA	4,439	302	(2) 3	50,400	5	610	14,620	8,810	19,360	424	52	8	430	18,210	2'-4 1/4"	14'-5"
	VRC-0243A-1212N-HA	5,027	342	(2) 5	59,800			14,630	8,810	19,370	424	52			18,230	2'-4 1/4"	14'-5"
	VRC-0268A-1212N-JA	5,542	377	(2) 7.5	68,400			14,700	8,810	19,440	424	52			18,290	2'-4 1/4"	14'-5"
	VRC-0287A-1212N-KA	5,939	404	(2) 10	75,300			14,720	8,810	19,460	424	52			18,310	2'-4 1/4"	14'-5"
	VRC-0271A-1212N-HA	5,601	381	(2) 5	59,800			16,280	10,460	21,120	525	64			19,980	2'-11 3/4"	15'-0"
	VRC-0298A-1212N-JA	6,174	420	(2) 7.5	68,400			16,350	10,460	21,190	525	64			20,040	2'-11 3/4"	15'-0"
	VRC-0320A-1212N-KA	6,630	451	(2) 10	73,100			16,370	10,460	21,210	525	64			20,060	2'-11 3/4"	15'-0"
	VRC-0349A-1212N-KA	7,218	491	(2) 10	71,200			18,950	13,040	23,950	683	84			22,790	3'-7"	15'-8"
	VRC-0384A-1212N-LA	7,953	541	(2) 15	81,500			19,130	13,040	24,130	683	84			22,970	3'-7"	15'-8"
	VRC-0412A-1212N-MA	8,526	580	(2) 20	89,700			19,180	13,040	24,180	683	84			23,020	3'-7"	15'-8"
	VRC-0381A-1212N-KA	7,894	537	(2) 10	67,300			20,750	14,840	25,870	794	97			24,710	4'-2 1/2"	16'-3"
	VRC-0415A-1212N-LA	8,600	585	(2) 15	77,100			20,930	14,840	26,050	794	97			24,890	4'-2 1/2"	16'-3"
	VRC-0445A-1212N-MA	9,202	626	(2) 20	85,200			20,980	14,840	26,100	794	97			24,940	4'-2 1/2"	16'-3"
	VRC-0469A-1212N-NA	9,717	661	(2) 25	91,800			21,290	14,840	26,410	794	97			25,250	4'-2 1/2"	16'-3"
	VRC-0417A-1218N-GB	8,638	588	(8) 2.6	101,700			19,080	12,530	26,160	632	77			24,370	2'-4 1/4"	14'-5"
	VRC-0467A-1218N-HB	9,652	657	(8) 4.3	119,900			19,170	12,530	26,250	632	77			24,460	2'-4 1/4"	14'-5"
12' x 18' - EC Fan System	VRC-0516A-1218N-JB	10,668	726	(8) 6.7	139,200	7.5	920	19,300	12,530	26,380	632	77	10	619	24,590	2'-4 1/4"	14'-5"
	VRC-0457A-1218N-GB	9,445	642	(8) 2.6	97,500			21,500	14,950	28,730	785	96			26,940	2'-11 3/4"	15'-0"
	VRC-0510A-1218N-HB	10,554	718	(8) 4.3	115,000			21,590	14,950	28,820	785	96			27,030	2'-11 3/4"	15'-0"
	VRC-0564A-1218N-JB	11,665	794	(8) 6.7	133,500			21,720	14,950	28,950	785	96			27,160	2'-11 3/4"	15'-0"
	VRC-0497A-1218N-GB	10,286	700	(8) 2.6	92,200			25,250	18,700	32,720	1,024	125			30,940	3'-7"	15'-8"
	VRC-0555A-1218N-HB	11,494	782	(8) 4.3	108,800			25,340	18,700	32,810	1,024	125			31,030	3'-7"	15'-8"
	VRC-0614A-1218N-JB	12,704	864	(8) 6.7	126,200			25,470	18,700	32,940	1,024	125			31,160	3'-7"	15'-8"
	VRC-0536A-1218N-GB	11,093	755	(8) 2.6	84,600			27,890	21,340	35,530	1,192	146			33,740	4'-2 1/2"	16'-3"
	VRC-0599A-1218N-HB	12,396	843	(8) 4.3	99,800			27,980	21,340	35,620	1,192	146			33,830	4'-2 1/2"	16'-3"
	VRC-0662A-1218N-JB	13,701	932	(8) 6.7	115,700			28,110	21,340	35,750	1,192	146			33,960	4'-2 1/2"	16'-3"
	VRC-0374A-1218N-HA	7,732	526	(3) 5	89,700			20,520	12,530	27,520	632	77			25,810	2'-4 1/4"	14'-5"
	VRC-0413A-1218N-JA	8,541	581	(3) 7.5	102,700			20,620	12,530	27,620	632	77			25,920	2'-4 1/4"	14'-5"
12' x 18' - BALTDRIIVE®	VRC-0442A-1218N-KA	9,158	623	(3) 10	113,000	7.5	920	20,660	12,530	27,660	632	77	10	619	25,950	2'-4 1/4"	14'-5"
	VRC-0414A-1218N-HA	8,555	582	(3) 5	87,000			22,940	14,950	30,090	785	96			28,380	2'-11 3/4"	15'-0"
	VRC-0456A-1218N-JA	9,437	642	(3) 7.5	99,600			23,040	14,950	30,190	785	96			28,490	2'-11 3/4"	15'-0"
	VRC-0489A-1218N-KA	10,114	688	(3) 10	109,700			23,080	14,950	30,230	785	96			28,520	2'-11 3/4"	15'-0"
	VRC-0533A-1218N-KA	11,025	750	(3) 10	106,800			26,830	18,700	34,220	1,024	125			32,520	3'-7"	15'-8"
	VRC-0587A-1218N-LA	12,157	827	(3) 15	122,200			27,100	18,700	34,490	1,024	125			32,780	3'-7"	15'-8"
	VRC-0630A-1218N-MA	13,039	887	(3) 20	134,500			27,160	18,700	34,550	1,024	125			32,860	3'-7"	15'-8"
	VRC-0636A-1218N-LA	13,157	895	(3) 15	115,000			29,740	21,340	37,300	1,192	146			35,580	4'-2 1/2"	16'-3"
	VRC-0680A-1218N-MA	14,068	957	(3) 20	126,100			29,800	21,340	37,360	1,192	146			35,660	4'-2 1/2"	16'-3"
	VRC-0717A-1218N-NA	14,847	1010	(3) 25	135,800			30,280	21,340	37,840	1,192	146			36,120	4'-2 1/2"	16'-3"


Vertex™ Evaporative Condenser Engineering Data




Face A: VRC 10' x 24' and 10' x 36'
EC Fan System Units




Face D: VRC 10' x 24'
EC Fan System Units




Face D: VRC 10' x 36'
EC Fan System Units



Face A: VRC 10' x 24' and 10' x 36'
Baltidrive® Power Train Units



Face D: VRC 10' x 24'
Baltidrive® Power Train Units



Face D: VRC 10' x 36' Units
Baltidrive® Power Train Units



NOTES:


1. Model number denotes nominal tons using R-717 tons are at a 96.3°F condensing temperature, a 20°F suction temperature, and a 78°F entering wet-bulb temperature.
2. R-22 tons are at a 105°F condensing temperature, a 40°F suction temperature, and a 78°F entering wet-bulb temperature.
3. Unless otherwise noted, the coil section is the heaviest section.
4. Operating weight is for the unit with the water level at the overflow level and with the coil charged with R-717.
5. The R-22 operating charge is 1.93 times the R-717 charge; R-134a is 1.98 times.
6. Drain size is based on a bottom connection.
7. Coil inlet and outlet connections are 4" beveled for welding.

Do not use for construction. Refer to factory certified dimensions. This catalog includes data current at the time of publication, which should be reconfirmed at the time of purchase.




Nom. Box Size	Model Number ⁽¹⁾	Base Heat Rejection (MBH)	R-22 Tons ⁽²⁾	Fan Motor (HP)	Airflow Rate (CFM)	Pump Motor (HP)	Spray Flow Rate (GPM)	Approximate Weight (lbs)			R-717 Operating Charge ⁽⁵⁾ (lbs)	Internal Coil Volume (ft ³)	Remote Sump			F	H
								Ship Weight	Heaviest Section ⁽³⁾	Oper. Weight ⁽⁴⁾			Drain Size ⁽⁶⁾ (in)	Volume Req. (gal)	Approx. Oper. Weight (lbs)		
10' x 24' - EC Fan System	VRC-0482A-1024N-GB	9,972	678	(12) 2.6	141,400	(2)5	500	23,980	7,350	32,660	689	84	(2)8	627	17,480	2'-4 1/4"	14'-5"
	VRC-0538A-1024N-HB	11,137	758	(12) 4.3	166,700			24,100	7,350	32,780	689	84			17,550	2'-4 1/4"	14'-5"
	VRC-0595A-1024N-JB	12,312	838	(12) 6.7	193,500			24,300	7,350	32,980	689	84			17,650	2'-4 1/4"	14'-5"
	VRC-0539A-1024N-GB	11,145	758	(12) 2.6	128,100			26,680	8,700	35,520	854	104			18,990	2'-11 3/4"	15'-0"
	VRC-0601A-1024N-HB	12,447	847	(12) 4.3	150,900			26,800	8,700	35,640	854	104			19,060	2'-11 3/4"	15'-0"
	VRC-0665A-1024N-JB	13,759	936	(12) 6.7	175,200			27,000	8,700	35,840	854	104			19,160	2'-11 3/4"	15'-0"
	VRC-0577A-1024N-GB	11,947	813	(12) 2.6	106,200			31,210	10,970	40,330	1132	138			21,540	3'-7"	15'-8"
	VRC-0646A-1024N-HB	13,342	908	(12) 4.3	125,100			31,330	10,970	40,450	1132	138			21,610	3'-7"	15'-8"
	VRC-0713A-1024N-JB	14,750	1003	(12) 6.7	145,200			31,530	10,970	40,650	1132	138			21,710	3'-7"	15'-8"
	VRC-0620A-1024N-GB	12,838	873	(12) 2.6	109,500			34,210	12,470	43,520	1316	161			23,220	4'-2 1/2"	16'-3"
	VRC-0693A-1024N-HB	14,338	975	(12) 4.3	129,100			34,330	12,470	43,640	1316	161			23,290	4'-2 1/2"	16'-3"
	VRC-0766A-1024N-JB	15,851	1078	(12) 6.7	149,800			34,530	12,470	43,840	1316	161			23,390	4'-2 1/2"	16'-3"
10' x 24' - BALTDRIIVE®	VRC-0470A-1024N-JA	9,732	662	(4) 7.5	137,000	(2)5	500	25,820	7,350	34,460	689	84	(2)8	627	18,400	3'-7"	14'-5"
	VRC-0484A-1024N-HA	9,996	680	(4) 5	110,800			28,380	8,700	37,180	854	104			19,850	4'-2 1/2"	15'-0"
	VRC-0533A-1024N-JA	11,026	750	(4) 7.5	126,800			28,520	8,700	37,320	854	104			19,910	4'-2 1/2"	15'-0"
	VRC-0571A-1024N-KA	11,818	804	(4) 10	139,600			28,560	8,700	37,360	854	104			19,930	2'-4 1/4"	15'-0"
	VRC-0609A-1024N-KA	12,612	858	(4) 10	120,000			33,090	10,970	42,170	1132	138			22,480	2'-4 1/4"	15'-8"
	VRC-0672A-1024N-LA	13,906	946	(4) 15	137,200			33,450	10,970	42,530	1132	138			22,660	2'-11 3/4"	15'-8"
	VRC-0615A-1024N-JA	12,730	866	(4) 7.5	114,200			36,050	12,470	45,320	1316	161			24,140	2'-11 3/4"	16'-3"
	VRC-0659A-1024N-KA	13,642	928	(4) 10	125,600			36,090	12,470	45,360	1316	161			24,160	2'-11 3/4"	16'-3"
	VRC-0727A-1024N-LA	15,052	1024	(4) 15	143,800			36,450	12,470	45,720	1316	161			24,340	3'-7"	16'-3"
10' x 36' - EC Fan System	VRC-0713A-1036N-GB	14,768	1005	(16) 2.6	194,300	(2)7.5	760	32,860	10,440	45,570	1026	125	(2)10	913	24,580	2'-4 1/4"	14'-5"
	VRC-0798A-1036N-HB	16,509	1123	(16) 4.3	229,200			33,040	10,440	45,750	1026	125			24,670	2'-4 1/4"	14'-5"
	VRC-0882A-1036N-JB	18,254	1242	(16) 6.7	266,000			33,300	10,440	46,010	1026	125			24,800	2'-4 1/4"	14'-5"
	VRC-0779A-1036N-GB	16,120	1097	(16) 2.6	180,500			36,820	12,420	49,780	1275	156			26,810	2'-11 3/4"	15'-0"
	VRC-0871A-1036N-HB	18,020	1226	(16) 4.3	212,900			37,000	12,420	49,960	1275	156			26,900	2'-11 3/4"	15'-0"
	VRC-0963A-1036N-JB	19,925	1355	(16) 6.7	247,100			37,260	12,420	50,220	1275	156			27,030	2'-11 3/4"	15'-0"
	VRC-0851A-1036N-GB	17,623	1199	(16) 2.6	148,300			43,430	15,730	56,810	1696	207			30,540	3'-7"	15'-8"
	VRC-0952A-1036N-HB	19,699	1340	(16) 4.3	175,000			43,610	15,730	56,990	1696	207			30,630	3'-7"	15'-8"
	VRC-1052A-1036N-JB	21,779	1482	(16) 6.7	203,000			43,870	15,730	57,250	1696	207			30,760	3'-7"	15'-8"
	VRC-0915A-1036N-GB	18,940	1288	(16) 2.6	151,900			47,820	17,920	61,480	1974	241			33,010	4'-2 1/2"	16'-3"
	VRC-1023A-1036N-HB	21,173	1440	(16) 4.3	179,100			48,000	17,920	61,660	1974	241			33,100	4'-2 1/2"	16'-3"
	VRC-1131A-1036N-JB	23,411	1593	(16) 6.7	207,900			48,260	17,920	61,920	1974	241			33,230	4'-2 1/2"	16'-3"
10' x 36' - BALTDRIIVE®	VRC-0653A-1036N-HA	13,524	920	(6) 5	175,400	(2)7.5	760	35,980	10,440	48,650	1026	125	(2)10	913	26,130	2'-11 3/4"	14'-5"
	VRC-0771A-1036N-KA	15,964	1086	(6) 10	221,000			36,260	10,440	48,930	1026	125			26,270	3'-7"	14'-5"
	VRC-0724A-1036N-HA	14,994	1020	(6) 5	174,400			39,940	12,420	52,860	1275	156			28,360	3'-7"	15'-0"
	VRC-0796A-1036N-JA	16,464	1120	(6) 7.5	191,400			40,140	12,420	53,060	1275	156			28,470	3'-7"	15'-0"
	VRC-0853A-1036N-KA	17,640	1200	(6) 10	210,600			40,220	12,420	53,140	1275	156			28,500	4'-2 1/2"	15'-0"
	VRC-0865A-1036N-JA	17,904	1218	(6) 7.5	163,600			46,750	15,730	60,090	1696	207			32,200	4'-2 1/2"	15'-8"
	VRC-0927A-1036N-KA	19,198	1306	(6) 10	180,000			46,830	15,730	60,170	1696	207			32,230	4'-2 1/2"	15'-8"
	VRC-1004A-1036N-KA	20,786	1414	(6) 10	188,400			51,220	17,920	64,840	1974	241			34,700	4'-2 1/2"	16'-3"
	VRC-1106A-1036N-LA	22,902	1558	(6) 15	215,800			51,760	17,920	65,380	1974	241			34,960	2'-4 1/4"	16'-3"


Vertex™ Evaporative Condenser Engineering Data




Face A: VRC 12' x 24' and 12' x 36'
EC Fan System Units




Face D: VRC 12' x 24'
EC Fan System Units




Face D: VRC 12' x 36'
EC Fan System Units



Face A: VRC 12' x 24' and 12' x 36'
Baltidrive® Power Train Units



Face D: VRC 12' x 24'
Baltidrive® Power Train Units



Face D: VRC 12' x 36' Units
Baltidrive® Power Train Units

NOTES:

1. Model number denotes nominal tons using R-717 tons are at a 96.3°F condensing temperature, a 20°F suction temperature, and a 78°F entering wet-bulb temperature.
2. R-22 tons are at a 105°F condensing temperature, a 40°F suction temperature, and a 78°F entering wet-bulb temperature.
3. Unless otherwise noted, the coil section is the heaviest section.
4. Operating weight is for the unit with the water level at the overflow level and with the coil charged with R-717.
5. The R-22 operating charge is 1.93 times the R-717 charge; R-134a is 1.98 times.
6. Drain size is based on a bottom connection.
7. Coil inlet and outlet connections are 4" beveled for welding.

Do not use for construction. Refer to factory certified dimensions. This catalog includes data current at the time of publication, which should be reconfirmed at the time of purchase.




Nom. Box Size	Model Number ⁽¹⁾	Base Heat Rejection (MBH)	R-22 Tons ⁽²⁾	Fan Motor (HP)	Airflow Rate (CFM)	Pump Motor (HP)	Spray Flow Rate (GPM)	Approximate Weight (lbs)			R-717 Operating Charge ⁽⁵⁾ (lbs)	Internal Coil Volume (ft³)	Remote Sump			F	H
								Ship Weight	Heaviest Section ⁽³⁾	Oper. Weight ⁽⁴⁾			Drain Size ⁽⁶⁾ (in)	Volume Req. (gal)	Approx. Oper. Weight (lbs)		
12' x 24' - EC Fan System	VRC-0562A-1224N-GB	11,638	792	(12) 2.6	144,600	(2) 5	610	27,670	8,810	37,200	848	104	(2) 8	860	21,430	2'-4 1/4"	14'-5"
	VRC-0628A-1224N-HB	12,998	884	(12) 4.3	170,400			27,790	8,810	37,320	848	104			21,490	2'-4 1/4"	14'-5"
	VRC-0695A-1224N-JB	14,369	977	(12) 6.7	197,800			27,990	8,810	37,520	848	104			21,590	2'-4 1/4"	14'-5"
	VRC-0621A-1224N-GB	12,859	875	(12) 2.6	139,200			30,970	10,460	40,700	1050	128			23,280	2'-11 3/4"	15'-0"
	VRC-0694A-1224N-HB	14,361	977	(12) 4.3	164,100			31,090	10,460	40,820	1050	128			23,340	2'-11 3/4"	15'-0"
	VRC-0767A-1224N-JB	15,876	1080	(12) 6.7	190,500			31,290	10,460	41,020	1050	128			23,440	2'-11 3/4"	15'-0"
	VRC-0676A-1224N-GB	14,002	953	(12) 2.6	131,000			36,130	13,040	46,170	1367	167			26,180	3'-7"	15'-8"
	VRC-0755A-1224N-HB	15,637	1064	(12) 4.3	154,400			36,250	13,040	46,290	1367	167			26,240	3'-7"	15'-8"
	VRC-0835A-1224N-JB	17,287	1176	(12) 6.7	179,300			36,450	13,040	46,490	1367	167			26,340	3'-7"	15'-8"
	VRC-0725A-1224N-GB	15,014	1021	(12) 2.6	121,800			39,740	14,840	50,010	1589	194			28,210	4'-2 1/2"	16'-3"
	VRC-0810A-1224N-HB	16,768	1141	(12) 4.3	143,600			39,860	14,840	50,130	1589	194			28,270	4'-2 1/2"	16'-3"
	VRC-0895A-1224N-JB	18,536	1261	(12) 6.7	166,700			40,060	14,840	50,330	1589	194			28,370	4'-2 1/2"	16'-3"
12' x 24' - BALTDRIIVE®	VRC-0429A-1224N-GA	8,878	604	(4) 3	100,800	(2) 5	610	29,230	8,810	38,720	848	104	(2) 8	860	22,210	4'-4 1/2"	14'-5"
	VRC-0486A-1224N-HA	10,054	684	(4) 5	119,500			29,250	8,810	38,740	848	104			22,230	4'-2 1/2"	14'-5"
	VRC-0535A-1224N-JA	11,084	754	(4) 7.5	136,800			29,390	8,810	38,880	848	104			22,290	4'-2 1/2"	14'-5"
	VRC-0574A-1224N-KA	11,878	808	(4) 10	150,600			29,430	8,810	38,920	848	104			22,310	4'-2 1/2"	14'-5"
	VRC-0541A-1224N-HA	11,202	762	(4) 5	119,600			32,550	10,460	42,240	1050	128			24,080	2'-4 1/4"	15'-0"
	VRC-0597A-1224N-JA	12,348	840	(4) 7.5	136,800			32,690	10,460	42,380	1050	128			24,140	2'-4 1/4"	15'-0"
	VRC-0641A-1224N-KA	13,260	902	(4) 10	146,200			32,730	10,460	42,420	1050	128			24,160	2'-4 1/4"	15'-0"
	VRC-0697A-1224N-KA	14,436	982	(4) 10	142,400			37,890	13,040	47,890	1367	167			27,060	2'-4 1/4"	15'-8"
	VRC-0768A-1224N-LA	15,906	1082	(4) 15	163,000			38,250	13,040	48,250	1367	167			27,240	2'-11 3/4"	15'-8"
	VRC-0824A-1224N-MA	17,052	1160	(4) 20	179,400			38,350	13,040	48,350	1367	167			27,290	2'-11 3/4"	15'-8"
	VRC-0763A-1224N-KA	15,788	1074	(4) 10	134,600			41,500	14,840	51,730	1589	194			29,090	3'-7"	16'-3"
	VRC-0831A-1224N-LA	17,200	1170	(4) 15	154,100			41,860	14,840	52,090	1589	194			29,270	3'-7"	16'-3"
	VRC-0889A-1224N-MA	18,404	1252	(4) 20	170,400			41,960	14,840	52,190	1589	194			29,320	3'-7"	16'-3"
	VRC-0939A-1224N-NA	19,434	1322	(4) 25	183,600			42,580	14,840	52,810	1589	194			29,630	4'-2 1/2"	16'-3"
12' x 36' - EC Fan System	VRC-0835A-1236N-GB	17,276	1175	(16) 2.6	203,300	(2) 7.5	920	38,150	12,530	52,320	1263	154	(2) 10	1,237	30,160	2'-4 1/4"	14'-5"
	VRC-0934A-1236N-HB	19,305	1313	(16) 4.3	239,800			38,330	12,530	52,500	1263	154			30,250	2'-4 1/4"	14'-5"
	VRC-1032A-1236N-JB	21,336	1451	(16) 6.7	278,300			38,590	12,530	52,760	1263	154			30,380	2'-4 1/4"	14'-5"
	VRC-0914A-1236N-GB	18,889	1285	(16) 2.6	195,000			42,990	14,950	57,460	1570	192			32,880	2'-11 3/4"	15'-0"
	VRC-1020A-1236N-HB	21,108	1436	(16) 4.3	230,000			43,170	14,950	57,640	1570	192			32,970	2'-11 3/4"	15'-0"
	VRC-1127A-1236N-JB	23,329	1587	(16) 6.7	266,900			43,430	14,950	57,900	1570	192			33,100	2'-11 3/4"	15'-0"
	VRC-0994A-1236N-GB	20,572	1399	(16) 2.6	184,400			50,490	18,700	65,440	2049	250			37,110	3'-7"	15'-8"
	VRC-1111A-1236N-HB	22,989	1564	(16) 4.3	217,500			50,670	18,700	65,620	2049	250			37,200	3'-7"	15'-8"
	VRC-1227A-1236N-JB	25,408	1728	(16) 6.7	252,400			50,930	18,700	65,880	2049	250			37,330	3'-7"	15'-8"
	VRC-1072A-1236N-GB	22,187	1509	(16) 2.6	169,100			55,770	21,340	71,060	2384	291			40,090	4'-2 1/2"	16'-3"
	VRC-1198A-1236N-HB	24,793	1687	(16) 4.3	199,500			55,950	21,340	71,240	2384	291			40,180	4'-2 1/2"	16'-3"
	VRC-1324A-1236N-JB	27,402	1864	(16) 6.7	231,400			56,210	21,340	71,500	2384	291			40,310	4'-2 1/2"	16'-3"
12' x 36' - BALTDRIIVE®	VRC-0661A-1236N-GA	13,675	930	(6) 3	151,400	(2) 7.5	920	41,010	12,530	55,010	1263	154	(2) 10	1237	31,600	2'-4 1/4"	14'-5"
	VRC-0747A-1236N-HA	15,464	1052	(6) 5	179,400			41,030	12,530	55,030	1263	154			31,600	2'-4 1/4"	14'-5"
	VRC-0825A-1236N-JA	17,082	1162	(6) 7.5	205,300			41,230	12,530	55,230	1263	154			31,710	2'-4 1/4"	14'-5"
	VRC-0885A-1236N-KA	18,316	1246	(6) 10	226,000			41,310	12,530	55,310	1263	154			31,740	2'-11 3/4"	14'-5"
	VRC-0912A-1236N-JA	18,874	1284	(6) 7.5	199,200			46,070	14,950	60,380	1570	192			34,430	2'-11 3/4"	15'-0"
	VRC-0977A-1236N-KA	20,228	1376	(6) 10	219,300			46,150	14,950	60,460	1570	192			34,460	2'-11 3/4"	15'-0"
	VRC-1065A-1236N-KA	22,050	1500	(6) 10	213,600			53,650	18,700	68,440	2049	250			38,690	3'-7"	15'-8"
	VRC-1175A-1236N-LA	24,314	1654	(6) 15	244,400			54,190	18,700	68,980	2049	250			38,950	3'-7"	15'-8"
	VRC-1260A-1236N-MA	26,078	1774	(6) 20	269,000			54,310	18,700	69,100	2049	250			39,030	3'-7"	15'-8"
	VRC-1271A-1236N-LA	26,314	1790	(6) 15	230,000			59,470	21,340	74,590	2384	291			41,930	4'-2 1/2"	16'-3"
	VRC-1359A-1236N-MA	28,136	1914	(6) 20	252,200			59,590	21,340	74,710	2384	291			42,010	4'-2 1/2"	16'-3"
	VRC-1434A-1236N-NA	29,694	2020	(6) 25	271,600			60,550	21,340	75,670	2384	291			42,470	4'-2 1/2"	16'-3"

Vertex™ Evaporative Condenser Structural Support

The recommended support arrangement for Vertex Evaporative Condensers consists of parallel structural members running the full length of the unit. In addition to providing adequate support, the members also serve to raise the unit above any solid foundation which might restrict air movement or prevent access to the unit. Refer to the BAC unit certified print for bolt hole location.

Center line distances between bolt holes are tabulated in the table below.

Model Number	D
VRC-x-1012-x	9'-7 1/2"
VRC-x-1018-x	9'-7 1/2"
VRC-x-1212-x	11'-7 1/4"
VRC-x-1218-x	11'-7 1/4"
VRC-x-1024-x	9'-7 1/2"
VRC-x-1036-x	9'-7 1/2"
VRC-x-1224-x	11'-7 1/4"
VRC-x-1236-x	11'-7 1/4"



NOTES:

1. Support members and anchor bolts shall be designed, furnished, and installed by others.
2. Design of support members and anchor bolts shall be in accordance with the strength and serviceability requirements of the applicable building code and project specifications.
3. Support members shall be level at the top.
4. Refer to the certified unit support drawing for loading and additional support requirements.
5. The length of the support members shall be at least equal to the length of the basin. Refer to Engineering Data for basin dimensions.
6. If vibration isolation (provided by others) is used, the isolators should be located under a structural base that complies with one of the recommended support arrangements. Contact your local BAC Representative for all other isolator configurations.