


Notes

- 1) All dimensions are in feet and inches. Weights are in pounds and do not include options and accessories.
- 2) Unless otherwise indicated, connections 3" and smaller are NPT. Connections 4" and larger are grooved to suit a mechanical coupling and beveled for welding.
- 3) Dimensions showing location of coil connections are approximate and should not be used for prefabrication of connecting piping.
- 4) For weight loadings and support requirements, refer to the suggested steel support drawing.
- 5) The area above the discharge must be unobstructed.
- 6) Piping must not be supported by the unit inlet or outlet connections.
- 7) M = Motor location, M1 = Large Motor Location, M2 = Small Motor Location



MODEL NO.	APPROX. SHIPPING WEIGHT	APPROX. OPERATING WEIGHT	HEAVIEST SECTION (COIL)	F	H
VCA-920A	35710	54110	12100	2'-9 1/4"	13'-9 1/2"
VCA-1086A	35970	54370	12100	2'-9 1/4"	13'-9 1/2"
VCA-1020A	40700	59370	14590	3'-6 1/2"	14'-6 3/4"
VCA-1120A	40890	59560	14590	3'-6 1/2"	14'-6 3/4"
VCA-1200A	40960	59630	14590	3'-6 1/2"	14'-6 3/4"
VCA-1062A	45690	64630	17090	4'-3 3/4"	15'-4"
VCA-1169A	45880	64820	17090	4'-3 3/4"	15'-4"
VCA-1240A	45950	64890	17090	4'-3 3/4"	15'-4"
VCA-1218A	48900	68030	18600	4'-3 3/4"	15'-4"
VCA-1306A	48970	68100	18600	4'-3 3/4"	15'-4"
VCA-1414A	54460	73880	21340	5'-1"	16'-1 1/4"
VCA-1558A	54880	74300	21340	5'-1"	16'-1 1/4"

ORDER NO:

DATE:



Baltimore Aircoil

VCA Unit Print  
10'x36' RH

DRAWING NUMBER: