


**Notes**

- 1) Unless otherwise indicated, connections 3" and smaller are NPT. Connections 4" and larger are grooved to suit a mechanical coupling and beveled for welding.
- 2) All dimensions are in feet and inches. Weights are in pounds and include options and accessories.
- 3) For weight loadings and support requirements, refer to the suggested steel support drawing.
- 4) The area above the fan discharge must be unobstructed.
- 5) Piping must not be supported by the tower inlet or outlet connections.
- 6) Unit weights include selected accessories.
- 7) M = Motor location.

Model Number	Shipping Weight	Operating Weight	Heaviest Section	"H"	"B"	"D"	"L"
PT2-1012A-1x2	11510	20700	4360	14'-3 1/4"	8'-5 1/4"	8'-4"	5'-4 3/8"
PT2-1012A-2x2	12320	21510	4740	15'-3 1/4"	9'-5 1/4"	9'-4"	5'-4 3/8"
PT2-1012A-3x2	13440	22630	5280	16'-3 1/4"	10'-5 1/4"	10'-4"	5'-4 3/8"
PT2-1012A-4x2	13930	24100	5280	18'-0 1/4"	12'-2 1/4"	10'-4"	7'-1 3/8"
PT2-1012A-5x2	14650	24820	5640	19'-0 1/4"	13'-2 1/4"	11'-4"	7'-1 3/8"



ORDER NO:

DATE:



**BALTIMORE  
AIRCOIL COMPANY**

**PT2 Two Cell Unit Print  
Internal Belt Drive**

DRAWING NUMBER:  
**GEN-PT2-1012A 2-CELL**