



NOTES:

1. Do not use for construction. Refer to factory certified dimensions.
2. Model number denotes R-717 capacity in evaporator tons at 96.3°F condensing temperature, 20°F suction temperature, and 78°F entering wet bulb temperature.
3. All dimensions are in feet and inches. Weights are in pounds. Volumes are in cubic feet.
4. Operating weight is for the base unit charged with R-717, water level in the cold water basin at overflow, and does not include accessories.
5. The actual size, quantity and location of the coil inlet and outlet connections will vary depending on the refrigerant used and capacity requirements.
6. The coil inlet and outlet connections are NPS beveled for welding as standard.
7. Models with Whisper Quiet fans may have heights up to 5 1/2" greater than shown.



Plan View

Do Not Obstruct Area Above Fans



Tabulated Unit Data

Model Number	Fan HP	Operating Wt	Shipping Wt	Heaviest Section	F	H	Coil Volume (FT ³)
CXVB-914-1236-30	30	66,880	42,860	14,210	6' 3 1/4"	19' 11 3/8"	58
CXVB-966-1236-30	30	76,760	52,210	18,660	6' 3 1/4"	19' 11 3/8"	87
CXVB-1027-1236-45	45	72,060	47,760	16,550	6' 3 1/4"	19' 11 3/8"	73
CXVB-1049-1236-45	45	77,000	52,440	18,770	6' 3 1/4"	19' 11 3/8"	87
CXVB-1049-1236-60	60	67,180	43,160	14,350	6' 3 1/4"	19' 11 3/8"	58
CXVB-1089-1236-60	60	72,120	47,830	16,580	6' 3 1/4"	19' 11 3/8"	73
CXVB-1134-1236-75	75	72,240	47,950	16,640	6' 3 1/4"	19' 11 3/8"	73
CXVB-1161-1236-75	75	77,180	52,620	18,860	6' 3 1/4"	19' 11 3/8"	87
CXVB-1202-1236-90	90	77,380	52,830	18,960	6' 3 1/4"	19' 11 3/8"	87
CXVB-1257-1236-120	120	73,100	48,800	17,040	6' 3 1/4"	19' 11 3/8"	73
CXVB-1287-1236-120	120	78,040	53,480	19,270	6' 3 1/4"	19' 11 3/8"	87

CXVB Evaporative Condenser
Tabulated Unit Print

BALTIMORE AIRCOIL COMPANY

Drawing Number:
CXVB-1236C-6-TUP

Rev:
-