



- Notes
- 1) Drawings are not to scale. All dimensions are in feet and inches.
 - 2) Unless otherwise indicated, connections 3" and smaller are MPT. Connections 4" and larger are grooved to suit a mechanical coupling and beveled for welding.
 - 3) Dimensions showing location of coil and basin connections are approximate and should not be used for prefabrication of connecting piping.
 - 4) For weight loadings and support requirements, refer to the suggested steel support drawing.
 - 5) Heaviest section is the combined weight of fan and coil sections, refer to the P-Series Counterflow Induced Draft Coil Products rigging and assembly manual for suggested lifting method.
 - 6) The area above the discharge must be unobstructed.
 - 7) Do not support piping from unit connections. All necessary piping supports to be supplied by others.
 - 8) M = Motor location

Model Number	Approx. Shipping Weight	Approx. Operating Weight	Heaviest Section Weight	F	H
PCC-1079-1240N080	47856	71650	19273	4'-0 5/8"	18'-11 7/16"
PCC-0855-1240N030	49660	73590	20173	4'-8 1/8"	19'-6 15/16"
PCC-0974-1240N040	54780	79020	22733	4'-8 1/8"	19'-6 15/16"
PCC-1071-1240N060	54940	79180	22813	4'-8 1/8"	19'-6 15/16"
PCC-1153-1240N080	55380	79620	23033	4'-8 1/8"	19'-6 15/16"
PCC-1218-1240N100	55430	79670	23058	4'-8 1/8"	19'-6 15/16"
PCC-1030-1240N040	62916	87780	26803	4'-0 5/8"	18'-11 7/16"
PCC-1105-1240N050	66916	92030	28803	4'-0 5/8"	18'-11 7/16"
PCC-1125-1240N060	63076	87940	26883	4'-0 5/8"	18'-11 7/16"
PCC-1151-1240N080	67016	92130	28853	4'-0 5/8"	18'-11 7/16"
PCC-1173-1240N080	60236	84890	25463	4'-0 5/8"	18'-11 7/16"
PCC-1234-1240N080	67456	92570	29073	4'-0 5/8"	18'-11 7/16"
PCC-1270-1240N100	63566	88430	27128	4'-0 5/8"	18'-11 7/16"
PCC-1308-1240N100	67506	92620	29098	4'-0 5/8"	18'-11 7/16"
PCC-1367-1240N120	68008	93120	29349	4'-0 5/8"	18'-11 7/16"

ORDER NO: _____

DATE: _____



PCC-Evaporative Condenser
 Tabulated Unit Print
 DRAWING NUMBER:
 UP-PCC-1240