




NOTES:

1. **Do not use for construction.** Refer to factory certified dimensions.
2. Nominal tons of cooling represents 3 USGPM of water cooled from 95°F to 85°F at a 78°F entering wet bulb temperature.
3. All dimensions are in feet and inches. Weights are in pounds. Volumes are in gallons.
4. Operating weight is for the base unit configuration with the water level in the cold water basin at overflow and does not include accessories.
5. The actual size, quantity and location of the coil inlet and outlet connections will vary depending on the design flow rate and pressure drop requirements.
6. The coil inlet and outlet connections are NPS beveled for welding.
7. Models with Whisper Quiet fans may have heights up to 5 1/2" greater than shown.



Plan View

Do Not Obstruct Area Above Fans



Tabulated Unit Data

Model Number	Operating Wt	Shipping Wt	Heaviest Section Wt	Coil Connection	F	Coil Volume (GAL)
FXV-1218B-12D-x	29,433	16,690	10,069	4"	3'-6 1/2"	217
FXV-1218B-16D-x	31,296	17,952	11,331	4"	3'-6 1/2"	289
FXV-1218B-16Q-x	31,663	18,319	11,698	6"	3'-4 1/2"	289
FXV-1218B-20D-x	32,870	18,924	12,303	4"	3'-6 1/2"	361
FXV-1218B-23Q-x	35,584	21,037	14,416	6"	3'-4 1/2"	432
FXV-1218B-23T-x	35,636	21,090	14,468	6"	3'-4 1/2"	432