



PLAN VIEW

PLAN "C" STEEL

Model Number	Shipping Weight	Operating Weight
PT2-1012A-1x3	17590	31370
PT2-1012A-2x3	18790	32570
PT2-1012A-3x3	20970	34750
PT2-1012A-4x3	21700	36960
PT2-1012A-5x3	22780	38040

Notes

- 1) All dimensions are in feet and inches. Weights are in pounds and include options and accessories.
- 2) Supporting steelwork and anchor bolts to be designed and furnished by others.
- 3) All supporting steel must be flush and level at top.
- 4) Each beam should be designed, as a minimum, for 65% of the total unit operating weight applied as a uniformly distributed load.
- 5) Beams should be selected in accordance with accepted structural practice, maximum deflection of beam under unit to be 1/360 of span, not to exceed 1/2 inch.
- 6) If vibration isolation rails are to be used between unit and supporting steel, be certain to allow for the length of the vibration rails when determining length of supporting steel. Vibration rail length and mounting hole locations may differ from those of the unit. Refer to vibration isolator drawings for this data.
- 7) Do not use this drawing to size point vibration isolators. See your BAC Representative for details.

ORDER NO:

DATE:



**BALTIMORE
AIRCOIL COMPANY**

**PT2 Three Cell Unit Support
Internal Belt Drive**

DRAWING NUMBER:
GEN-PT2-1012A-SS 3-CELL