


Notes  
1)

Model Number	Approx. Shipping Weight	Approx. Operating Weight	Heaviest Section Weight	F	H
PCC-2159-2440N160	96120	143700	19273	4'-0 5/8"	20'-5 7/16"
PCC-1710-2440N060	99728	147590	20173	4'-8 1/8"	21'-0 15/16"
PCC-1948-2440N080	109968	158450	22733	4'-8 1/8"	21'-0 15/16"
PCC-2143-2440N120	110288	158770	22813	4'-8 1/8"	21'-0 15/16"
PCC-2306-2440N160	111168	159650	23033	4'-8 1/8"	21'-0 15/16"
PCC-2436-2440N200	111268	159750	23058	4'-8 1/8"	21'-0 15/16"
PCC-2060-2440N080	126240	175960	26803	4'-0 5/8"	20'-5 7/16"
PCC-2210-2440N100	134240	184460	28803	4'-0 5/8"	20'-5 7/16"
PCC-2250-2440N120	126560	176280	26883	4'-0 5/8"	20'-5 7/16"
PCC-2302-2440N120	134440	184660	28853	4'-0 5/8"	20'-5 7/16"
PCC-2345-2440N160	120880	170180	25463	4'-0 5/8"	20'-5 7/16"
PCC-2468-2440N160	135320	185540	29073	4'-0 5/8"	20'-5 7/16"
PCC-2540-2440N200	127540	177260	27128	4'-0 5/8"	20'-5 7/16"
PCC-2615-2440N200	135420	185640	29098	4'-0 5/8"	20'-5 7/16"
PCC-2734-2440N240	136424	186650	29349	4'-0 5/8"	20'-5 7/16"

Notes

- 1) Drawings are not to scale. All dimensions are in feet and inches.
- 2) Unless otherwise indicated, connections 3" and smaller are MPT. Connections 4" and larger are grooved to suit a mechanical coupling and beveled for welding.
- 3) Dimensions showing location of coil and basin connections are approximate and should not be used for prefabrication of connecting piping.
- 4) For weight loadings and support requirements, refer to the suggested steel support drawing.
- 5) Heaviest section is the combined weight of fan and coil sections, refer to the P-Series Counterflow Induced Draft Coil Products rigging and assembly manual for suggested lifting method.
- 6) The area above the discharge must be unobstructed.
- 7) Do not support piping from unit connections. All necessary piping supports to be supplied by others.
- 8) M = Motor location



ORDER NO:

DATE:



BALTIMORE  
AIRCOIL COMPANY

PCC Evaporative Condensator  
Tabulated Unit Print

DRAWING NUMBER:  
UP-PCC-2440