



MODEL NO.	APPROX. SHIPPING WEIGHT	APPROX. OPERATING WEIGHT
VCA-460A	17770	26970
VCA-507A	17870	27070
VCA-543A	17900	27100
VCA-510A	20260	29600
VCA-560A	20360	29700
VCA-600A	20390	29730
VCA-585A	22860	32330
VCA-620A	22890	32360
VCA-488A	24240	33800
VCA-609A	24370	33930
VCA-653A	24400	33960
VCA-707A	27150	36860
VCA-779A	27360	37070

Notes

- 1) All dimensions are in feet and inches. Weights are in pounds and do not include options and accessories.
- 2) Supporting steelwork and anchor bolts to be designed and furnished by others.
- 3) All supporting steel must be flush and level at top.
- 4) Each beam should be designed, as a minimum, for 65% of the total unit operating weight applied as a uniformly distributed load.
- 5) Beams should be selected in accordance with accepted structural practice, maximum deflection of beam under the unit to be 1/360 of span, not to exceed 1/2 inch.
- 6) If vibration isolation rails are used between unit and supporting steel, be certain to allow for the length of the vibration rails when determining length of supporting steel. Vibration rail length and mounting hole locations may differ from those of the unit. Refer to vibration isolator manufacturer drawings for this data.
- 7) Do not use this drawing to size point vibration isolators.

ORDER NO: _____

DATE: _____



Baltimore Aircoil

VCA Unit Support
10'x18'

DRAWING NUMBER: _____