



MODEL NO.	APPROX. SHIPPING WEIGHT	APPROX. OPERATING WEIGHT	HEAVIEST SECTION (COIL)	F	H
VCA-526A	20030	31730	14360	2'-9 1/4"	13'-9 1/2"
VCA-581A	20060	31760	14360	2'-9 1/4"	13'-9 1/2"
VCA-623A	20070	31770	14360	2'-9 1/4"	13'-9 1/2"
VCA-582A	23020	34880	17350	3'-6 1/2"	14'-6 3/4"
VCA-642A	23050	34910	17350	3'-6 1/2"	14'-6 3/4"
VCA-688A	23060	34920	17350	3'-6 1/2"	14'-6 3/4"
VCA-602A	26010	38030	20340	4'-3 3/4"	15'-4"
VCA-664A	26040	38060	20340	4'-3 3/4"	15'-4"
VCA-711A	26050	38070	20340	4'-3 3/4"	15'-4"
VCA-785A	26130	38150	20340	4'-3 3/4"	15'-4"
VCA-751A	27940	40070	22230	4'-3 3/4"	15'-4"
VCA-827A	28020	40150	22230	4'-3 3/4"	15'-4"
VCA-887A	28160	40290	22230	4'-3 3/4"	15'-4"
VCA-895A	31230	43540	25440	5'-1"	16'-1 1/4"
VCA-957A	31370	43680	25440	5'-1"	16'-1 1/4"
VCA-1010A	31500	43810	25440	5'-1"	16'-1 1/4"

Notes

- 1) All dimensions are in feet and inches. Weights are in pounds and do not include options and accessories.
- 2) Unless otherwise indicated, connections 3" and smaller are NPT. Connections 4" and larger are grooved to suit a mechanical coupling and beveled for welding.
- 3) Dimensions showing location of coil connections are approximate and should not be used for prefabrication of connecting piping.
- 4) For weight loadings and support requirements, refer to the suggested steel support drawing.
- 5) The area above the discharge must be unobstructed.
- 6) Piping must not be supported by the unit inlet or outlet connections.
- 7) M = Motor location, M1 = Large Motor Location, M2 = Small Motor Location

ORDER NO:

DATE:



Baltimore Aircoil

VCA Unit Print

12'x18' RH

DRAWING NUMBER: