



MODEL NO.	APPROX. SHIPPING WEIGHT	APPROX. OPERATING WEIGHT
VCA-662A	24750	36900
VCA-680A	27990	40310
VCA-750A	28110	40430
VCA-804A	28160	40480
VCA-760A	31470	43970
VCA-814A	31520	44020
VCA-858A	33460	46080
VCA-946A	33740	46360
VCA-866A	37090	49910
VCA-928A	37140	49960
VCA-1024A	37420	50240
VCA-S700A	27250	39570
VCA-S828A	27420	39740
VCA-S838A	30730	43230
VCA-S884A	32790	45410

Notes

- 1) All dimensions are in feet and inches. Weights are in pounds and do not include options and accessories.
- 2) Supporting steelwork and anchor bolts to be designed and furnished by others.
- 3) All supporting steel must be flush and level at top.
- 4) Each beam should be designed, as a minimum, for 65% of the total unit operating weight applied as a uniformly distributed load.
- 5) Beams should be selected in accordance with accepted structural practice, maximum deflection of beam under the unit to be 1/360 of span, not to exceed 1/2 inch.
- 6) If vibration isolation rails are used between unit and supporting steel, be certain to allow for the length of the vibration rails when determining length of supporting steel. Vibration rail length and mounting hole locations may differ from those of the unit. Refer to vibration isolator manufacturer drawings for this data.
- 7) Do not use this drawing to size point vibration isolators.

ORDER NO: \_\_\_\_\_

DATE: \_\_\_\_\_



Baltimore Aircoil

VCA Unit Support  
10'x24'

DRAWING NUMBER: \_\_\_\_\_