



PLAN VIEW

PLAN "C" STEEL

Model Number	Shipping Weight	Operating Weight
PT2-1214A-1x2	14150	26580
PT2-1214A-2x2	15450	27880
PT2-1214A-3x2	16440	28860
PT2-1214A-4x2	16920	29920
PT2-1214A-5x2	17900	30900

- Notes
- 1) All dimensions are in feet and inches. Weights are in pounds and include options and accessories.
 - 2) Supporting steelwork and anchor bolts to be designed and furnished by others.
 - 3) All supporting steel must be flush and level at top.
 - 4) Each beam should be designed, as a minimum, for 65% of the total unit operating weight applied as a uniformly distributed load.
 - 5) Beams should be selected in accordance with accepted structural practice, maximum deflection of beam under unit to be 1/360 of span, not to exceed 1/2 inch.
 - 6) If vibration isolation rails are to be used between unit and supporting steel, be certain to allow for the length of the vibration rails when determining length of supporting steel. Vibration rail length and mounting hole locations may differ from those of the unit. Refer to vibration isolator drawings for this data.
 - 7) Do not use this drawing to size point vibration isolators. See your BAC Representative for details.

ORDER NO: _____

DATE: _____



PT2 Two Cell Unit Support
Internal Belt Drive

DRAWING NUMBER:
GEN-PT2-1214A-SS 2-CELL