


MODEL NO.	APPROX. SHIPPING WEIGHT	APPROX. OPERATING WEIGHT	HEAVIEST SECTION (COIL)	F	H
VCA-460A	17770	26970	12010	2'-9 1/4"	13'-9 1/2"
VCA-507A	17870	27070	12010	2'-9 1/4"	13'-9 1/2"
VCA-543A	17900	27100	12010	2'-9 1/4"	13'-9 1/2"
VCA-510A	20260	29600	14500	3'-6 1/2"	14'-6 3/4"
VCA-560A	20360	29700	14500	3'-6 1/2"	14'-6 3/4"
VCA-600A	20390	29730	14500	3'-6 1/2"	14'-6 3/4"
VCA-585A	22860	32330	17000	4'-3 3/4"	15'-4"
VCA-620A	22890	32360	17000	4'-3 3/4"	15'-4"
VCA-488A	24240	33800	18510	4'-3 3/4"	15'-4"
VCA-609A	24370	33930	18510	4'-3 3/4"	15'-4"
VCA-653A	24400	33960	18510	4'-3 3/4"	15'-4"
VCA-707A	27150	36860	21260	5'-1"	16'-1 1/4"
VCA-779A	27360	37070	21260	5'-1"	16'-1 1/4"

- Notes
- 1) All dimensions are in feet and inches. Weights are in pounds and do not include options and accessories.
 - 2) Unless otherwise indicated, connections 3" and smaller are NPT. Connections 4" and larger are grooved to suit a mechanical coupling and beveled for welding.
 - 3) Dimensions showing location of coil connections are approximate and should not be used for prefabrication of connecting piping.
 - 4) For weight loadings and support requirements, refer to the suggested steel support drawing.
 - 5) The area above the discharge must be unobstructed.
 - 6) Piping must not be supported by the unit inlet or outlet connections.
 - 7) M = Motor location, M1 = Large Motor Location, M2 = Small Motor Location



ORDER NO:

DATE:



VCA Unit Print
10'x18' RH
DRAWING NUMBER: